


NOTES: UNLESS OTHERWISE SPECIFIED

- CONSTRUCTION:
 HOUSING: NYLON. AVAILABLE IN ALL TEN COLORS.
 FRAME: NICKEL PLATED BRASS.
 CONTACT: NICKEL PLATED BeCu OR PHOSPHOR BRONZE.
 EYELET: BRASS
 TERMINAL RING: TIN PLATED COPPER.
 SOCKET: NICKEL PLATED BRASS.

- PERFORMANCE:
 MAXIMUM CURRENT: 15 AMPS
 MAXIMUM TEMPERATURE: 200°F (93°C)

		REVISIONS	
LTR	DESCRIPTION	DATE	APPROVED



		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE: FRACTIONS DECIMALS ANGLES ± .XX ± ± .XXX ±	CONTRACT NO.		E-Z-HOOK DIVISION OF TEKTEST INC. ARCADIA, CA 91006 U.S.A.			
			APPROVALS	DATE				
		MATERIAL SEE NOTE.	DRAWN	S.B.W.	7/05	DESCRIPTION SHROUDED R/A STD BANANA PLUG		
			APPROVED BY					
		FINISH SEE NOTE.			SIZE	CODE IDENT NO.	DRAWING NO.	REV.
NEXT ASSY	USED ON				A	08505	9306	
APPLICATION		DO NOT SCALE DRAWING			SCALE	1:1	SHEET 1 OF 1	