

BU-P5167-@

(4mm In-line Banana Jack with Insulator)



- Mueller's BU-P5167 is an in-line, insulated, 4mm banana jack used for making testing cables and field repairs.
- Connects to wire up to from 18-22 AWG via solder or crimp connection.
- Overall length 1.5" (38.1mm), outer diameter = 0.35" (8.89mm)

Material: Banana jack Nickel-plated brass

Insulator Flexible PVC

• Ratings: Current 15 Amps

Voltage Hands-free testing to 30VAC/60VDC Max.

Toll Free: 800.955.2629

Phone: 330.780.2525 Fax: 330.780.2524

Temperature 50°C (122°F) Max.

Color: The "@" in the model number represents color.

Available colors: -0 Black, -2 Red

RoHS 3 compliant, exemption 6c