

HR600755

Electrical Specification @25°C

RoHS Compliant (Pb Free)

Isolation: 2750Vrms 1mA 60S (Pri to Sec)

Pin1-3 Inductance: 275 uH Min. @100KHz 10mVrms

Pin1-3 DC Resistance: 0.30 ohms Max. Pin6-4 DC Resistance: 0.35 ohms Max.


Turns Ratio: Pin1-3: Pin6-4 = 1CT: $1.1CT \pm 2\%$ @100KHz 10mVrms

Current Rating: 150mA


E-T Prod(V-uS): 9.44 Min.

Operating Temperature: $-40^{\circ}\text{C} \sim +125^{\circ}\text{C}$ Including temperature rise

Schematics



Mechanical Dimensions



Unless otherwise specified, Tol.: .xx \pm 0.25 (mm)

REV.: 00 1 of 1

Address: No.16, Industrial Road Central, Industrial Zone, Xiaolan Town,
Zhongshan City, Guangdong Province, China
Tel: (0760)22126805 22132332 Fax: (0760)22132339 Post code: 528416
E-Mail: sales@hanrun.com http://www.hanrun.com

Specifications subject to change without notice. Refer to the approval sheet for lastly edition.