





REV.	Q'TY	ECN. NO.	APR.	DATE




RECOMMENDED PCB LAYOUT TOP VIEW (TOLERANCE:±0.05)
RECOMMENDED METAL MASK T=0.12mm



- 1) MATERIAL:
HOUSING:LCP S475 UL 94V-0
CONTACT:C5191
SHELL:SUS304-H
- 2) FINISH:
CONTACT:GOLD FLASH PLATED ON CONTACT AREA;
GOLD FLASH PLATED ON SOLDER TAILS,
- 3) ELECTRICAL CHARACTERISTICS
RATING CURRENT : 0.5A MAX.
CONTACT RESISTANCE :50 mΩ MAX
DIELECTRIC WITHSTANDING : 500V AC MIN.
INSULATION RESISTANCE: 1000 MΩ MIN.
- 4) MECHANICAL CHARACTERISTICS
MATING CYCLE :3000 CYCLES

SIM pin Assignment	
PIN#	Name
C1	VCC
C2	RST
C3	CLK
C5	GND
C6	VPP
C7	I/O



DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED		TITLE: 1.35H 6PIN PUSH PUSH MICRO SIM CARD CONNECTOR			
.X±0.35	.X*±5°	APR.	Alex	DWG NO. SIM202G-ZYB6AH1.35	
.XX±0.25	.X*±3°	CHK.	Jack	PROJ. CUSTOMER DRAWING	
.XXX±0.15	.XX*±1°	DRA.	Can	SIZE A4	SCALE 1:1
				SHEET 1/1	REV. A