



NOTES:

1. 材质: PBT+30%GF  
 端子: C2680R-EH, T=0.20±0.01  
 SHELL: C2680-1/2H, T=0.30±0.01.

Specification

- 1.ELECTRICAL CHARACTERISTIC:  
 CONTACT RESISTANCE: 30mΩ Max  
 DIELECTRIC WITHSTANDING VOLTAGE: 500V AC for 1MIN  
 INSULATION RESISTANCE: 1000MΩ Min
- 2.MECHANICAL CHARACTERISTIC:  
 INSERTION FORCE: 35N(3.57KgF) MAX  
 EXTRACTION FORCE: 10~35N(1.02~3.57KgF)  
 DURABILITY: 1500 CYCLES
- 3.ENVIRONMENTAL:  
 OPERATING TEMPERATURE: -55°C~+85°C

- 4.△为品管必须管控尺寸.
- 5.⊕为巡检尺寸.
- 6.整套成品配合需顺畅.
- 7.所有的功能测试要满足USB协会 2.0版本.

|            |                      |            |            |               |               |
|------------|----------------------|------------|------------|---------------|---------------|
| 版本<br>REV. | 變更內容<br>MODIFICATION | 日期<br>DATE | 修改<br>DRAW | 核准<br>APPROVE | 審核<br>CHECKED |
|------------|----------------------|------------|------------|---------------|---------------|

|             |                |                            |
|-------------|----------------|----------------------------|
| 單位<br>UNIT  | MM             | 深圳市连欣科技有限公司                |
| 比例<br>SCALE | 1:1            |                            |
| 張數<br>SHEET | 1/1            | 料号<br>PART NO.             |
| 製圖<br>DRAWN | 李生             | 名稱<br>TITLE                |
|             | .X±0.30 X'±3'  | AP 00° 側鎖解快L=10.0寬邊(中心脚0距) |
|             | .XX±0.25 X'±1' | 角法<br>PROV.                |
|             | .XXX±0.10 XX'± | 成品圖                        |