



PCB LAYOUT

注：\*标识表示重点尺寸

MATERIAL

Insulator :PA6T+30%G. F(UL94V-0)

Contact :Brass

Contact Plating:Gold over 40u" Nickel

Color : Black

Plating:1.0-3.0u"Au

SPECIFICATION

Current Rate : 3Amp

Operation Temperature:-40;°C to +105;°C

Contact Resistance: 20mΩ MAX.

Insulation Resistance: 1000MΩ MIN.at DC 500V

Dielectirc Strength:AC 500V Per minute

PIN Number	Dimension(mm)		PIN Number	Dimension(mm)	
	A	B		A	B
2*1P	.....	.....	2*21P	50.80	60.94
2*2P	.....	.....	2*22P	53.34	63.48
2*3P	5.08	15.22	2*23P	55.88	66.02
2*4P	7.62	17.76	2*24P	58.42	68.56
2*5P	10.16	20.30	2*25P	60.96	71.10
2*6P	12.70	22.84	2*26P	63.50	73.64
2*7P	15.24	25.38	2*27P	66.04	76.18
2*8P	17.78	27.92	2*28P	68.58	78.72
2*9P	20.32	30.46	2*29P	71.12	81.26
2*10P	22.86	33.00	2*30P	73.66	83.80
2*11P	25.40	35.54	2*31P	76.20	86.34
2*12P	27.94	38.08	2*32P	78.74	88.88
2*13P	30.48	40.62	2*33P	81.28	91.42
2*14P	33.02	43.16	2*34P	83.82	93.96
2*15P	35.56	45.70	2*35P	86.36	96.50
2*16P	38.10	48.24	2*36P	88.90	99.04
2*17P	40.64	50.78	2*37P	91.44	101.58
2*18P	43.18	53.32	2*38P	93.98	104.12
2*19P	45.72	55.86	2*39P	96.52	106.66
2*20P	48.26	58.40	2*40P	99.06	109.20



# L&X 深圳市连欣科技有限公司

<b>X.±0.25</b>	<b>XX±0.15</b>	Item Specification	BOX/筒牛PH2.54MM直插座系列		
<b>XXX±0.05</b>	<b>XXXX±0.01</b>	Drawing NO.	XDFH-0254-2*_N_P		
<b>X*±1°</b>	<b>XX*±0.05°</b>	DRAWING	Gao Zhong Yan	CHECKED	APPROVE
SCALE: 1:1	SIZE: A4	EDITION	B/0	DATE	2017-03-27