



注：本板为禁止传输、复制、编辑文档，以及用其内容进行交流



NOTES1:
UL Standard

1. Use group	B	C	D
Rated Current	8A	/	8A
Rated Voltage	300V	/	300V

2. Wire range: 28~16AWG
IEC Standard

1. Pollution Degree	3	2	2
Overvoltage Category	III	III	II
Rate Impulse Voltage(KV)	2.5KV	2.5KV	2.5KV
Rate Voltage(V)	160V	160V	320V
Rate Current(A)	8A	8A	8A

NOTES2:


- 1.Housing: PA66 (UL94V-0)
- 2.Cover: PA66 (UL94V-0)
- 3.Clamp: Copper alloy (Ni Plated)
- 4.Cage: Brass (Ni Plated)
- 5.Screw1: Steel (M2,Zn Plated)
- 6.Screw1: Steel (M2.5,Zn Plated)

NOTES3:

- 1.Pitch: 3.81mm Poles: 02-24P
- 2.Stripping length: 6-7mm
- 3.Operating temperature: -40°C~+105°C
- 4.RoHS Compliance

How to order

MX15EDGKAM - 3.81 - XXP - XXXX - XX - X - X



Pitch Range In mm

Over	Nominal Dimension	Range
6 TO	10 TO	24 TO
10 TO	30 TO	60 TO
15 TO	60 TO	100 TO
20 TO	100 TO	150 TO
25 TO	150 TO	150 TO

mm

ITEM	NAME OF PART	NO. OF PART	Q'TY	MATERIAL	NOTE
DWG	CHK	DATE	SCALE	SHEET/OF	1/1
APP	DATE	SCALE	1:1	A4	
CIXI MAIXU ELECTRONICS CO.,LTD			MX15EDGKAM-3.81-XXP		
慈溪市迈旭电子有限公司			DWGNO.		