



SPECIFICATIONS

Current Rating: 3Amps
 Insulation Resistance: 1000MΩ Min
 Contact Resistance: 20mΩ Max
 Withstanding Voltage: AC 1000V
 Operation Temperature: -40° to +105°
 Contact Material: Brass
 Standard: PA6T
 Insulator Material: Polyester(UL 94V-0)
 Contact Plating: Gold Flash
 Max.Processing Temp: 240°C for 30-60seconds
 (260°C for 5seconds)


P/N	PIN	DIM.A	DIM.B
PH2.54-07-01PWD	1	0.00	2.54
PH2.54-07-02PWD	2	2.54	5.08
PH2.54-07-03PWD	3	5.08	7.62
PH2.54-07-04PWD	4	7.62	10.16
PH2.54-07-05PWD	5	10.16	12.70
PH2.54-07-06PWD	6	12.70	15.24
PH2.54-07-07PWD	7	15.24	17.78
PH2.54-07-08PWD	8	17.78	20.32
PH2.54-07-09PWD	9	20.32	22.86
.....
PH2.54-07-40PWD	40	(PIN-1)X2.54	(PIN)X2.54



PART NUMBER DESCRIPTION:

PH2.54-07-NPWD

(D=单排; S=双排)
 (Z=直脚; W=弯脚)
 (PIN数量; 01.....40PIN)
 (排针开关)



MANUFACTURE DWG		东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE: 2.54PH H2.5 1xnPin 90度 PC3.0 PA6.0 PB4.3 L13.8 6T 弯脚面
DECIMALS:	ANGLES:		PAR PH2.54-07-NPWD DWN CHKD APVD
X.±0.30	X°±5'	SCALE N:A	UNIT:MM
X.X±0.20	X.X°±1'	SIZE:A4	UNIT:MM
X.XX±0.10	X.XX°±0.5'	CUSTOMER COPY	SHEET: 1F1 REV:A