

ATGBICS SFP-25G-SR-RGD Cisco Compatible Transceiver SFP28 25GBase-SR (850nm, MMF, 100m, DOM, Ind Temp)

Brand : ATGBICS

Product code: SFP-25G-SR-RGD-C

Product name : SFP-25G-SR-RGD Cisco Compatible Transceiver SFP28 25GBase-SR (850nm, MMF, 100m, DOM, Ind Temp)



SFP-25G-SR-RGD Cisco Compatible Transceiver SFP28 25GBase-SR (850nm, MMF, 100m, DOM, Ind Temp)

ATGBICS SFP-25G-SR-RGD Cisco Compatible Transceiver SFP28 25GBase-SR (850nm, MMF, 100m, DOM, Ind Temp):

ATGBICS SFP-25G-SR-RGD 25GBase-SR supports a distance of up to 100m over multi-mode fibre (MMF) using a wavelength of 850nm via an LC connector. This product is suitable for rugged environments and can operate at temperatures between -40C to +85C. Digital optical monitoring (DOM) support is also present enabling real-time monitoring of the parameters of the fibre optic transceiver. Our product meets the specification of Cisco SFP-25G-SR-RGD= and we proudly offer a compatibility guarantee and lifetime warranty. Our rigorously tested products record a unique traceable serial number and are fully compliant with all MSA Standards.



| Performance | | Power | |
|--|---------------------|-----------------------------------|-------------|
| SFP transceiver type * | Fiber optic | Input voltage | 3.3 V |
| Maximum data transfer rate * | 25000 Mbit/s | Maximum voltage | 3.5 V |
| Interface type * | SFP28 | Power consumption (typical) | 1 W |
| Single-mode fiber (SMF) supported | ✗ | Operational conditions | |
| Multi-mode fiber (MMF) supported | ✓ | Minimum operating temperature | -40 °C |
| Fiber optic connector | LC | Maximum operating temperature | 85 °C |
| SFP transceiver standard | SR | Operating temperature (T-T) | -40 - 85 °C |
| Maximum transfer distance | 100 m | Storage temperature (T-T) | -40 - 85 °C |
| Wavelength | 850 nm | Operating relative humidity (H-H) | 0 - 95% |
| Ethernet LAN | ✓ | Storage relative humidity (H-H) | 0 - 95% |
| Ethernet interface type | 25 Gigabit Ethernet | Weight & dimensions | |
| Digital Diagnostics Monitoring (DDM) | ✓ | Width | 13.4 mm |
| Wavelength-division multiplexing (WDM) | ✗ | Depth | 56.5 mm |
| Features | | Height | 8.5 mm |
| Product colour | Silver | Weight | 20 g |
| Housing material | Metal | Packaging data | |
| Plug and Play | ✓ | Number of products included | 1 pc(s) |
| Hot-Plug support | ✓ | Package type | Box |
| Hot-swap | ✓ | Technical details | |
| Easy to install | ✓ | Sustainability compliance | ✓ |
| Country of origin | United Kingdom | Sustainability certificates | RoHS |
| Brand compatibility | Cisco | Doesn't contain | Lead |
| Certification | CE, FCC, RoHS | | |



5056468746979

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.