

ATGBICS FTLC1122RDNL Finisar Compatible Transceiver CFP2 Module 100GBase-LR4 (1310nm, SMF, 10km, LC, DOM)

Brand : ATGBICS

Product code: FTLC1122RDNL-C

Product name : FTLC1122RDNL Finisar Compatible Transceiver CFP2 Module 100GBase-LR4 (1310nm, SMF, 10km, LC, DOM)



FTLC1122RDNL Finisar Compatible Transceiver CFP2 Module 100GBase-LR4 (1310nm, SMF, 10km, LC, DOM)

ATGBICS FTLC1122RDNL Finisar Compatible Transceiver CFP2 Module 100GBase-LR4 (1310nm, SMF, 10km, LC, DOM). SFP transceiver type: Fiber optic, Maximum data transfer rate: 100000 Mbit/s, Interface type: CFP2. Product colour: Silver, Country of origin: United Kingdom, Brand compatibility: Finisar.

Number of products included: 1 pc(s), Package type: Box



| Performance | | Features | |
|--------------------------------------|----------------------|-----------------------------------|----------------|
| SFP transceiver type * | Fiber optic | Hot-Plug support | ✓ |
| Maximum data transfer rate * | 100000 Mbit/s | Hot-swap | ✓ |
| Interface type * | CFP2 | Easy to install | ✓ |
| Single-mode fiber (SMF) supported | ✓ | Country of origin | United Kingdom |
| Multi-mode fiber (MMF) supported | ✗ | Brand compatibility | Finisar |
| Fiber optic connector | LC | Certification | CE, FCC, RoHS |
| SFP transceiver standard | LR4 | Operational conditions | |
| Maximum transfer distance | 10000 m | Maximum operating temperature | 70 °C |
| Wavelength | 1310 nm | Operating temperature (T-T) | 0 - 70 °C |
| Ethernet LAN | ✓ | Storage temperature (T-T) | -40 - 85 °C |
| Ethernet interface type | 100 Gigabit Ethernet | Operating relative humidity (H-H) | 5 - 85% |
| Networking standards | IEEE 802.3ba | Storage relative humidity (H-H) | 5 - 85% |
| Fiber ethernet cabling technology | 100GBASE | Packaging data | |
| Digital Diagnostics Monitoring (DDM) | ✓ | Number of products included | 1 pc(s) |
| Features | | Package type | Box |
| Product colour | Silver | Technical details | |
| Plug and Play | ✓ | Sustainability compliance | ✓ |
| | | Sustainability certificates | RoHS |
| | | Doesn't contain | Lead |



5056468767158

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 26-JAN-2024. Prints or copies of Information are only valid on the printed Publication date