

ATGBICS JD089A-T H3C Compatible Transceiver SFP 100Base-T (Copper RJ45, 100m)

Brand : ATGBICS

Product code: JD089A-T-C

Product name : JD089A-T H3C Compatible Transceiver SFP 100Base-T (Copper RJ45, 100m)



JD089A-T H3C Compatible Transceiver SFP 100Base-T (Copper RJ45, 100m)

ATGBICS JD089A-T H3C Compatible Transceiver SFP 100Base-T (Copper RJ45, 100m):

ATGBICS JD089A-T 100BASE-T SFP operates on standard Category 5 unshielded twisted-pair copper cabling of link lengths up to 100m. H3C 100BASE-T SFP modules support 10/100 auto negotiation and auto MDI/MDIX. Our product meets the specification of H3C JD089A-T= and we proudly offer a compatibility guarantee and lifetime warranty. Our rigorously tested products record a unique traceable serial number and are fully compliant with all MSA Standards.



ATGBICS JD089A-T H3C Compatible Transceiver SFP 100Base-T (Copper RJ45, 100m). SFP transceiver type: Copper, Maximum data transfer rate: 100 Mbit/s, Interface type: SFP. Product colour: Silver, Housing material: Metal, Country of origin: United Kingdom. Input voltage: 3.3 V, Maximum voltage: 4 V, Power consumption (typical): 1.3 W. Width: 13.4 mm, Depth: 56.5 mm, Height: 8.5 mm. Number of products included: 1 pc(s), Package type: Box

Performance		Features	
SFP transceiver type *	Copper	Certification	CE, FCC, RoHS
Maximum data transfer rate *	100 Mbit/s	Power	
Interface type *	SFP	Input voltage	3.3 V
Single-mode fiber (SMF) supported	✗	Maximum voltage	4 V
Multi-mode fiber (MMF) supported	✗	Power consumption (typical)	1.3 W
SFP transceiver standard	TX	Operational conditions	
Maximum transfer distance	100 m	Maximum operating temperature	70 °C
Ethernet LAN	✓	Operating temperature (T-T)	0 - 70 °C
Ethernet interface type	Fast Ethernet	Storage temperature (T-T)	-40 - 85 °C
Copper ethernet cabling technology	100BASE	Operating relative humidity (H-H)	5 - 85%
Auto MDI/MDI-X	✓	Storage relative humidity (H-H)	5 - 85%
Digital Diagnostics Monitoring (DDM)	✗	Weight & dimensions	
Features		Width	13.4 mm
Product colour	Silver	Depth	56.5 mm
Housing material	Metal	Height	8.5 mm
Plug and Play	✓	Weight	20 g
Hot-Plug support	✓	Packaging data	
Hot-swap	✓	Number of products included	1 pc(s)
Easy to install	✓	Package type	Box
Country of origin	United Kingdom	Technical details	
Brand compatibility	H3C	Sustainability compliance	✓
		Sustainability certificates	RoHS
		Doesn't contain	Lead



5056468746856

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.