

ATGBICS AFCT-5179BZ (3.3V) Avago Broadcom Compatible Transceiver 1x9 Transceiver for ATM, SONET OC-3/SDH STM-1, Black Case (1300nm, 125Mbps, SMF, SC, 3.3V Std Temp)



Brand : ATGBICS

Product code: AFCT-5179BZ-3.3V-C

Product name : AFCT-5179BZ (3.3V) Avago Broadcom Compatible Transceiver 1x9 Transceiver for ATM, SONET OC-3/SDH STM-1, Black Case (1300nm, 125Mbps, SMF, SC, 3.3V Std Temp)

AFCT-5179BZ (3.3V) Avago Broadcom Compatible Transceiver 1x9 Transceiver for ATM, SONET OC-3/SDH STM-1, Black Case (1300nm, 125Mbps, SMF, SC, 3.3V Std Temp)

[ATGBICS AFCT-5179BZ \(3.3V\) Avago Broadcom Compatible Transceiver 1x9 Transceiver for ATM, SONET OC-3/SDH STM-1, Black Case \(1300nm, 125Mbps, SMF, SC, 3.3V Std Temp\):](#)

ATGBICS AFCT-5179BZ (3.3V Version) 1x9 Transceiver is for ATM, SONET OC-3/SDH STM-1 applications. It supports a data transmission over single-mode fibre (SMF) using a wavelength of 1300nm via an SC connector. This product operates at a standard temperature range of 0°C to +70°C. Our product meets the specification of Avago Broadcom AFCT-5179BZ= (3.3V version) and we proudly offer a compatibility guarantee and lifetime warranty. Our rigorously tested products record a unique traceable serial number and are fully compliant with all MSA Standards.

The OEM (Avago Broadcom, Foxconn) version of this product is now obsolete. We can help extend the operational life of your equipment by supporting you with a third party alternative.

Performance		Features	
Maximum data transfer rate *	125 Mbit/s	Country of origin	United Kingdom
Single-mode fiber (SMF) supported	✓	Brand compatibility	Avago Technologies
Multi-mode fiber (MMF) supported	✗	Compatible products	AFCT-5179BZ
Fiber optic connector	SC	Certification	CE, FCC, RoHS
Wavelength	1300 nm	Power	
Coarse Wavelength Division Multiplexing (CWDM)	✗	Input voltage	3.3 V
Auto MDI/MDI-X	✗	Operational conditions	
Digital Diagnostics Monitoring (DDM)	✗	Maximum operating temperature	70 °C
Features		Operating temperature (T-T)	0 - 70 °C
Product colour	Black	Storage temperature (T-T)	-40 - 85 °C
Plug and Play	✓	Packaging data	
Hot-swap	✓	Number of products included	1 pc(s)
Easy to install	✓	Package type	Box
		Technical details	
		Sustainability compliance	✓
		Sustainability certificates	RoHS
		Doesn't contain	Lead



5056468751720

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 26-JAN-2024. Prints or copies of Information are only valid on the printed Publication date