SPECIFICATIONS:

Insulation Resistance: $500M\Omega$ min. at 500V DC Withstanding Voltage: 500Vrms for 1min

Voltage Rating: 50Vrms AC Current Rating: 0.5A

Contact Resistance: 50mΩ max. at 20mV max.

Operating Temp.: - 40°C ~ +60°C

Mating Cycle: 20 times

MATERIALS AND FINISH:

• Contacts: Copper Alloy

Actuator: PA9TInsulator: LCP

SMT Tabs: Copper Alloy


3Gbps Tranmission

PART NUMBER:

2 = White

4 = Black


HF601-XX-XX



FEATURES:


- · ZIF type mating interface
- · Audible click feedback on locking
- Supports transmission speed up to 3Gbps for LVDS, HDMI, SATA signals
- · RoHS and REACH Compliant


OUTLINE DIMENSIONS (mm):



20	9.50	14.70	15.50
26	12.50	17.70	18.50
10	4.50	9.70	10.50
60	29.50	34.70	35.50
50	24.50	29.70	30.50
45	22.00	27.20	28.00
40	19.50	24.70	25.50
30	14.50	19.70	20.50
芯数(n)	Lp	L1	L2

HF601 R/A Mount Ver.





20	9.50	6.00	14.44
50	24.50	8.00	29.44
45	22.00	8.00	26.94
40	19.50	8.00	24.44
30	14.50	8.00	19.44
芯数(n)	Lр	L1	L2

HF601 Vertical Mount Ver.

Yamaichi Electronics USA Inc. Visit Us @ WWW.YEU.COM Email: Info@yeu.com TEL: 408-715-9100

YAMAICHI ELECTRONICS

FFC, FPC Cable Connectors HF601 Series

HF601 FFC/FPC Connectors

ZIF Style Connector Design

 Transmission speed: 1 ~ 3Gbps (HF601-22-03 only)

Pitch: 0.50 mm

Available Pin Count: 10 – 60pins



Product PN	Available Pin Count	Description	Design Option
HF601-XX-02	10, 20, 26, 30, 40, 45, 50, 60	Receptacle Connectors	Right Angle Mount
HF601-XX-12	20, 30, 40, 45, 50	Receptacle Connectors	Vertical Mount
HF601-22-03	22	Receptacle Connectors	Right Angle Mount

CAU002 HF601 Support Cable

• FFC/FPC Cable Designs

Offering various pin count options
 (20 ~ 50pin)



Product PN	Available Pin Count	Description	Design Option
CAU002-XXX-	20, 30, 40, 50	HF601 Series Support	0.5mm Pitch,
050-XXXX		FFC/FPC Cable	100/600/900mm L