

SPECIFICATIONS:

ELECTRICAL:

COAXIAL PINS:

50 OHM

MECHANICAL:

CONTACT INSERTION FORCE: 4.5 Kg Max. CONTACT SEPARATOR FORCE: 0.3Kg Min.

MATERIALS:

CONTACTS: COPPER ALLOY INSULATOR: PBT UL94V-0 RATED,

BLACK

STEEL


230°C PROCESS TEMP.

SHELL:

FINISH:

SHELL: NICKEL

CONTACTS: FULL GOLD FLASH



685M8W8203L<u>46</u>1

46 = 4-40 INSERTS / BOARD LOCKS

RoHS COMPLIANT

M.

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NOrComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:

M. SIGMON

DATE:

03/10/2014

UNITS = INCHES [MM] DO NOT SCALE FROM DRAWING



SCALE:						
NTS						
DWC NO:						

OF 2


2


REV

2

685M8W8203L461

SHEET





ROHS COMPLIANT

及

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:

M. SIGMON

DATE:

03/10/2014

UNITS = INCHES [MM]

DO NOT SCALE FROM DRAWING

NorComp

_		ا كاكلك	л пп		ш	
	SCALE:	SHEET		OF		REV
	NTS		2		2	2

685M8W8203L461