



			1	
	Part Number:		DRAWN	7/24/2010
MM033	2002 4	CJ	7/24/2018	
	14114102	3802 -4	CHECKED	8/16/2018
			C.H.	
	Description:	1S Microphone	APPROVED	8/16/2018
	Analog MEM		C.E.	

This document contains data proprietary to DB Unlimited. Any use or reproduction, in any form, without prior written permission of DB Unlimited is prohibited. All terms and conditions can be found at www.dbunlimitedco.com


Top View



Side View



Bottom View



Pin 1	Pin 2	Pin 3	Pin 4
OUTPUT	GND	VDD	GND

Items	Specifications	Conditions					
Directivity	Omnidirectional						
Sensitivity	-38 ± 1	dB					
Frequency Range	100 ~ 10,000	Hz					
Rated Voltage	2	V					
Voltage Range	1.6 ~ 3.6	V	REVISION HISTORY				
Output Impedance	300	Ω	REV	DESCRIPTION	DATE	APPROVED	
Max. Rated Current	0.18	mA		Released from Engineering	8/16/2018	C.E.	
Power Supply Rejection	-72	dB		NOTES		·	
Storage Temperature	-40 ~ +105	°C		All dimensions are in mm unless otherwise noted			
Operating Temperature	-40 ~ +105	°C		2) All tolerances are ± 0.1 mm unless otherwise noted			
Signal to Noise Ratio	63	dB		3) All parts meet RoHS			
Mount Type	Surface Mount			4) Subject to change or redrawn without notice			
Connection Method	Surface Mount Pads						
4 3 Additional considerations can be found at www.dbunlimitedco.com/technical-articl							