



Part Number:		DRAWN	7/25/2010	
NANAOO	3802-8	CJ	7/25/2018	
14114103		CHECKED	8/16/2018	
		C.H.		
Description:	IC Missaulassas	APPROVED	8/16/2018	
Analog MEN	1S Microphone	C.E.	0/10/2010	

This document contains data proprietary to DB Unlimited. Any use or reproduction, in any form, without prior written permission of DB Unlimited is prohibited. All terms and conditions can be found at www.dbunlimitedco.com


Top View



Side View



Bottom View



Pin 1	Pin 2	Pin 3	Pin 4	Pin 5	Pin 6
VDD	GND	GND	OUTPUT	GND	GND

Items	Specifications	Conditions						
Directivity	Omnidirectional							
Sensitivity	-38 ± 1	dB						
Frequency Range	30 ~ 10,000	Hz						
Rated Voltage	2	V						
Voltage Range	1.6 ~ 3.6	V		REVISION HISTORY				
Output Impedance	300	Ω	REV	DESCRIPTION	DATE	APPROVED		
Max. Rated Current	0.1	mA		Released from Engineering	8/16/2018	C.E.		
Power Supply Rejection	-90	dB		NOTES				
Storage Temperature	-40 ~ +105	°C		1) All dimensions are in mm unless otherwise noted				
Operating Temperature	-40 ~ +105	°C		2) All tolerances are ± 0.1 mm unless otherwise noted				
Signal to Noise Ratio	65	dB		3) All parts meet RoHS				
Mount Type	Surface Mount			4) Subject to change or redrawn without notice				
Connection Method	Surface Mount Pads							