

SPECIFICATIONS:

Insulation Resistance: 1,000MΩ min. at 500V DC Withstanding Voltage: 1,000Vrms for 1min Voltage Rating: 335V AC Current Rating: 1.0A MAX Contact Resistance: 5mQ max. at 20mV max. Operating Temp.: - 40°C ~ +105°C Mating Cycle: 25 times

PART NUMBER:

<u>HF106P-0012-0X</u> -VE		
	♦ 4	• •
Series Name		
RA Mount 1pin		

Key Codes:

Key M: Orange

Other Key Codes currently under development

MATERIALS AND FINISH:


Insulator: Heat Resistance Plastic Contacts:


- Outer Contact: Zinc Alloy
- Center Contact: Copper Alloy



- USCAR-18 Guidelines Compliant
- USCAR-17 Physical Stress Test Compliant
- · RA SMT Mount


OUTLINE DIMENSIONS:





Top View

RECOMMENDED PCB LAYOUT:



AUTOMOTIVE

COMPLIANT

© 2020 Yamaichi Electronics USA Incorporated. All brand or product names may be trademarks of their respective companies. Yamaichi Electronics USA Inc. Visit Us @ WWW.YEU.COM Email: Info@yeu.com TEL: 408-715-9100