





STRAIGHT MALE RECEPTACLE. P.C.B.

PAGE 1/2 ISSUE 11-06-15A SERIES SSLB PART NUMBER 7309-1511-000



All dimensions are in mm.





Technical Data Sheet

STRAIGHT MALE RECEPTACLE. P.C.B.

PAGE 2/2	ISSUE 11-06-15A	SERIES SSLB	PART NUMBER 7309-1511-000
-----------------	-----------------	--------------------	----------------------------------

PACKAGING

100	Contact us	Contact us
Standard	Unit	Other

ELECTRICAL CHARACTERISTICS

Impedance Ω Frequency 0-12.4 GHz

x F(GHz) Maxi √F(GHz) dB Maxi VSWR 0.0000 Insertion loss NA - F(GHz)) dB Maxi RF leakage NA - (Voltage rating 250 Veff Maxi

Dielectric withstanding voltage NA Veff mini Insulation resistance 1000 $M\Omega$ mini

MECHANICAL CHARACTERISTICS

Center contact retention

Axial force – Mating End Axial force – Opposite end 8.9 N mini N mini 8.9 Torque N.cm mini

Recommended torque

Mating NA N.cm Panel nut NA N.cm

Mating life 500 Cycles mini 0.3100 Weight

ENVIRONMENTAL

-65/+165 °С Operating temperature Hermetic seal NA Atm.cm3/s

Panel leakage NA

SPECIFICATION

OTHER CHARACTERISTICS

Assembly instruction:

Others: