







Recommended Mounting Layout

Dielectric Withstanding Voltage: 500 Vrms MAX

Operating Temperature: -55°C to 85°C Storage Temperature: -60°C to 165°C Center Contact Resistance: 3 mΩ MAX Outer Contact Resistance: 2 mΩ MAX Insulation Resistance: 2000 mΩ MIN

OHS MPLIANT	SI	UN	TS	

SMA PANEL MOUNT FEMALE STRAIGHT CONNECTOR

Document History			FEMALE STRAIGHT CONNECTOR			UK		
Edits Made	Date	Edited By	Approved By	Part No.	REV.	Drawn		Page
Initial Release	02/02/2021	B. Gibbons	KH Mun	SCNRF-6A		B. Gibbo	ns 02/02/2021	
				Drawing No.	SCALE	Checked		
					None	KH Mi	ın 02/02/2021	1/1
				Tolerance	UNIT	Approved		1/1
					mm	KH Mi	ın 02/02/2021	