



Wire-end ferrules, Max. wire cross-section: 25 mm², Length: 30 mm, Length of copper pipe: 16 mm, Colour: Brown

Business data

Article number	2267.0
Article name	H 25,0/30 BN
GTIN (EAN)	4044211050764
Packaging unit	50
Quantity unit	PC
Weight per piece (not including packaging)	1.19 g
Weight per piece (including packaging)	1.2 g
Unit of weight	G
Customs number	85369010
Country of origin	DE
Product description	Ferrules
Colour	Brown

Technical data

Dimensions

Length	30 mm
Length of copper pipe	16 mm
Diameter of copper pipe	7.3 mm
Diameter plastic collar	11.2 mm
Wall thickness of copper pipe	0.2 mm
Wall thickness of plastic collar	0.4 mm

Connection data

Wire cross-section, max.	25 mm ²
Wire cross-section AWG, max.	4
Stripping length	18 mm

Materials

Copper pipe	Copper alloy
Surface	Galvanically tin-plated, shiny
Plastic collar	Polypropylene homopolymer
Working temperature, min.	-5 °C
Working temperature, max.	105 °C

Further technical data

Insulation available	✓
----------------------	---

Environmental Product Compliance

REACH Conform	yes
REACH Reference date	2023-06-14
REACH Candidate Substance Note	No
RoHS Conform	yes

Data sheet

2267.0 H 25,0/30 BN



Approvals

Standards and regulations

DIN 46228-4:1990	yes
------------------	-----

Data sheet

2267.0 H 25,0/30 BN



Media

Accessories
