



PANEL CUT OUT

REVISIONS						
REV.	DESCRIPTION	DATE	APPROVED			
А	INITIAL RELEASE	03/05/18	D.N.			



	inches			
	Maxi	mini		
A	.198	.192		
В	.183	.177		



NOTES:

MATERIALS:

- 1. INSULATORS = VIRGIN WHITE TEFLON PER ASTM D1710, GRADE 1, TYPE I, CLASS "B".
 2. LOCKWASHER = PHOSPHOR BRONZE PER ASTM B139, COPPER ALLOY C53400, TEMPER H04.
 3. ALL OTHER METAL PARTS = BRASS PER ASTM B16, ALLOY C36000, TEMPER H02.

FINISHES:

- 1. CONTACT = GOLD PLATE PER ASTM B488-11, TYPE II, 50µin MIN, GRADE C, OVER 100 TO 200µin STRESS FREE SULFAMATE NICKEL PER AMS-QQ-N-290.

 2. ALL OTHER METAL PARTS = GOLD PLATE PER ASTM B488-11, TYPE II, 30µin MIN, GRADE C OVER 100 TO 200µin COPPER STRIKE PER AMS 2418.

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON DECIMAL ANGLE		DWN: D.N. CHKD:	DATE 03/05/18 DATE	communicated to a third party without prior a RADIALL company written permission of RADIALL. SMC STRAIGHT MALE JACK BULKHEAD REAR MOUNT CLAMP TYPE					
		C.E. APVD: J.M.	03/05/18 DATE 03/05/18						
REFERENCE: ORIGINATED: D.N.		MATERIALS & FI SEE N		size A	FSCM NO. 19505	DWG NO. 1003-1	551	-003	rev A
DATE: 03/05/18					6:1	THIRD ANGLE PROJECTION		SHEET 1 O	F 1