







STRAIGHT JACK RECEPTACLE FOR PCB SOLDER LEGS

PAGE 1/3 ISSUE **03-03-17B** SERIES **BNC 75 HDTV** PART NUMBER **R142500740**









All dimensions are in mm.



COMPONENTS	MATERIALS	PLATING (μm)
Body	ZAMAK	NICKEL .
Center contact	BERYLLIUM COPPER	GOLD OVER NICKEL
Outer contact		
Insulator	PTFE	
Gasket		
Others parts		
-	-	-
-	-	-



Technical Data Sheet

STRAIGHT JACK RECEPTACLE FOR PCB SOLDER LEGS

PAGE 2/3 ISSUE 03-03-17B SERIES BNC 75 HDTV PART NUMBER R142500740

PACKAGING

60	Contact us	Contact us
Standard	Unit	Other

ELECTRICAL CHARACTERISTICS

 $\begin{array}{ccc} \text{Impedance} & \textbf{75} & \Omega \\ \text{Frequency} & \textbf{DC-12} & \text{GHz} \end{array}$

 VSWR
 *1.05
 +
 0.0350
 x F(GHz) Maxi

 Insertion loss
 0.1*
 √F(GHz) dB Maxi

 RF leakage
 - (
 -57**
 - F(GHz)) dB Maxi

 Voltage rating
 500
 Veff Maxi

 Pickettic with changing wit

 $\begin{array}{cccc} \mbox{Voltage rating} & \mbox{500} & \mbox{Veff Maxi} \\ \mbox{Dielectric withstanding voltage} & \mbox{1500} & \mbox{Veff mini} \\ \mbox{Insulation resistance} & \mbox{5000} & \mbox{M}\Omega \mbox{ mini} \\ \end{array}$

MECHANICAL CHARACTERISTICS

Center contact retention

 Axial force – Mating End
 18
 N mini

 Axial force – Opposite end
 10
 N mini

 Torque
 NA
 N.cm mini

Recommended torque

Mating NA N.cm Panel nut NA N.cm

Mating life 500 Cycles mini Weight 3.5800 g

ENVIRONMENTAL

Operating temperature -65/+165 °C
Hermetic seal NA Atm.cm3/s
Panel leakage NA

SPECIFICATION

OTHER CHARACTERISTICS

Assembly instruction:NA

Others:

Data speed rate up to 12.5 Gb/s *Coaxial Transmission Line Only **Interface only





STRAIGHT JACK RECEPTACLE FOR PCB SOLDER LEGS

