



PANEL CUT OUT

REVISIONS						
REV.	DESCRIPTION	DATE	APPROVED			
А	INITIAL RELEASE	04/10/18	C.E.			



	inc	inches		
	Maxi	mini		
A	.198	.192		
В	.183	.177		



NOTES:

MATERIALS:

- 1. INSULATORS = VIRGIN WHITE TEFLON PER ASTM D1710, GRADE 1, TYPE I, CLASS "B".
 2. LOCKWASHER = PHOSPHOR BRONZE PER ASTM B139, COPPER ALLOY C53400, TEMPER H04.
 3. ALL OTHER METAL PARTS = BRASS PER ASTM B16, ALLOY C36000, TEMPER H02.

FINISHES:

- 1. CONTACT = GOLD PLATE PER ASTM B488-11, TYPE II, 50µin MIN, GRADE C, OVER 100 TO 200µin STRESS FREE SULFAMATE NICKEL PER AMS-QQ-N-290.

 2. ALL OTHER METAL PARTS = NICKEL PLATE PER AMS-QQ-N-290, CLASS 1, GRADE G, EXCEPT 100 TO 200µin THICK OVER 50 TO 100µin THICK COPPER PER AMS 2418.

UNLESS OTHERWISE SPE DIMENSIONS ARE IN IN TOLERANCES ON	ECIFIED ICHES	C.E. 04/10/	18	Property of Radiall This document cannot be reproduced or communicated to a third party without prior			
		CHKD: DATE		a RADIALL companywritten permission of RADIALL.			
DECIMAL A	ANGLE	D.N. 04/10/	18		SMB	STRAIGHT MALE JACK	
		APVD: DATE		BULKHEAD MOUNT CRIMP TYPE			
		J.M. 04/10/	18	FO	R RG-	-316 & SIMILAR CABLES	
REFERENCE:		MATERIALS & FINISHES:	ヿ	SIZE	FSCM NO.	DWG NO.	
		CEE NOTEC		А	19505	2003-7551-003	
ORIGINATED: C.E. DATE: 04/10/18		SEE NOTES		SCALE	6:1	THIRD ANGLE SHEET 1 OF 1	