






STRAIGHT JACK RECEPTACLE SOLDER LEGS - FULL DETENT

PAGE 1/2 ISSUE **04-01-17B** SERIES **SMP** PART NUMBER **R222426020**







All dimensions are in mm.



COMPONENTS	MATERIALS	PLATING (μm)
Body	STAINLESS STEEL	GOLD 0.5 OVER NICKEL 2
Center contact	BERYLLIUM COPPER	GOLD 1.27 OVER NICKEL 1.27
Outer contact		
Insulator	PTFE	
Gasket		
Others parts		
-	-	-
-	-	-



Technical Data Sheet

STRAIGHT JACK RECEPTACLE SOLDER LEGS - FULL DETENT

PAGE 2/2	ISSUE 04-01-17B	SERIES SMP	PART NUMBER R222426020
-----------------	------------------------	-------------------	-------------------------------

PACKAGING

100	Contact us	Contact us
Standard	Unit	Other

ELECTRICAL CHARACTERISTICS

MECHANICAL CHARACTERISTICS

Center contact retention

Axial force - Mating End
Axial force - Opposite end
Torque

6.8 N mini
NA N mini
N mini
N n.cm mini

Recommended torque

Mating NA N.cm Panel nut NA N.cm

Mating life 100 Cycles mini Weight 0,7200 g

ENVIRONMENTAL

Operating temperature -65/+165 °C
Hermetic seal NA Atm.cm3/s
Panel leakage NA

SPECIFICATION

OTHER CHARACTERISTICS

Assembly instruction:

Others:

*Coaxial Transmission Line Only

**DC-12 Ghz (Coaxial Transmission Line Only)

***Performance strongly depends on layout and PCB material