



REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
Α	INITIAL RELEASE	03/26/18	C.E.





NOTES:

MATERIALS:

- BODY & COUPLING NUT = BRASS PER ASTM B16, ALLOY C36000, TEMPER H02.
 INSULATOR = VIRGIN WHITE TEFLON PER ASTM D1710, GRADE 1, TYPE I, CLASS "B".
 CONTACT = BERYLLIUM COPPER PER ASTM B196, ALLOY C17300, TEMPER TD04.

FINISHES:

- BODY & COUPLING NUT = GOLD PLATE PER ASTM B488-11, TYPE II, 30µin MIN, GRADE C OVER 100 TO 200µin COPPER STRIKE PER AMS 2418.

 CONTACT = GOLD PLATE PER ASTM B488-11, TYPE II, 50µin MIN, GRADE C, OVER 100 TO 200µin STRESS FREE SULFAMATE NICKEL PER AMS-QQ-N-290.

UNLESS OTHERWISE SPECIFI DIMENSIONS ARE IN INCHE TOLERANCES ON	C.E. 03/26/18	communicated to a third party without prior	
10221000020 010	CHKD: DATE	a RADIALL company written permission of RADIALL.	
DECIMAL ANGL	E D.N. 03/26/18	SMC STRAIGHT FEMALE PLUG	
	APVD: DATE	P.C.B. MOUNT	
	J.M. 03/26/18	RECEPTACLE	
REFERENCE:	MATERIALS & FINISHES:	SIZE FSCM NO. DWG NO. REV	
ORIGINATED: C.E.	SEE NOTES	A 19505 1025-1511-000 A	
DATE: 03/26/18	SEE NOTES	SCALE 6:1 THIRD ANGLE SHEET 1 OF 1	