


REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	04/22/10	A.D.M.





NOTES:

MATERIALS:

1. BODY = STAINLESS STEEL PER ASTM A582, ALLOY 303, CONDITION "A".
2. INSULATOR = VIRGIN WHITE TEFLON PER ASTM D1710, GRADE 1, TYPE I, CLASS "B".
3. CONTACT = BERYLLIUM COPPER PER ASTM B196, ALLOY C17300, TEMPER TD04.

FINISHES:

1. BODY = PASSIVATE PER QQ-P-35, TYPE VI.
2. CONTACT = GOLD PLATE PER MIL-G-45204, TYPE II, CLASS 1, GRADE C, OVER .00010 TO .00020 STRESS FREE SULFAMATE NICKEL PER QQ-N-290.

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON	DWN: A.D.M.	DATE: 04/22/10	 Property of Radial This document cannot be reproduced or communicated to a third party without prior written permission of RADIAL.			
	CHKD: D.N.	DATE: 04/22/10				
	DECIMAL	ANGLE	APVD: J.M.	DATE: 04/22/10	SMA STRAIGHT JACK (4) HOLE FLANGE MOUNT RECEPTACLE	
REFERENCE:	MATERIALS & FINISHES: SEE NOTES	SIZE: A	FSCM NO.: 19505	DWG NO.: 9504-9113-031		
ORIGINATOR: A.D.M. DATE: 04/22/10		SCALE: 5:1	THIRD ANGLE PROJECTION 		SHEET 1 OF 1	

9504-9113-031