


## PANEL CUT OUT

	<u> </u>	<del>-</del>				
	inc	inches				
	Maxi	mini				
A	.509	.505				
В	.475	.471				

	REVISIONS					
REV.	DESCRIPTION	DATE	APPROVED			
Α	INITIAL RELEASE	05/09/18	D.N.			



## NOTES:

## MATERIALS:

- 1. INSULATORS = VIRGIN WHITE TEFLON PER ASTM D1710, GRADE 1, TYPE I, CLASS "B".
  2. CONTACT AND FERULE = BERYLLIUM COPPER PER ASTM B196, ALLOY C17300, TEMPER TD04.
  3. LOCKWASHER = PHOSPHOR BRONZE PER ASTM B139, COPPER ALLOY C53400, TEMPER H04.
  4. GASKET = SILICONE RUBBER 45 55 DUROMETER DOW CORNING SILASTIC 250.
  5. ALL OTHER METAL PARTS = BRASS PER ASTM B16, ALLOY C36000, TEMPER H02.

## FINISHES:

- 1. CONTACT & WIRE ADAPTER = GOLD PLATE PER ASTM B488-11, TYPE II, 50µin MIN, GRADE C, OVER 100 TO 200µin STRESS FREE SULFAMATE NICKEL PER AMS-QQ-N-290.

  2. ALL OTHER METAL PARTS = NICKEL PLATE PER AMS-QQ-N-290, CLASS 1, GRADE G, EXCEPT 100 TO 200µin THICK OVER 50 TO 100µin THICK COPPER PER AMS 2418.

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON		DWN: DATE D.N. 05/09/ CHKD: DATE	/18		,	Property of Radiall This document cannot be reproduced or communicated to a third party without prior written permission of RADIALL.
DECIMAL	DECIMAL ANGLE C.E. 05/09/18 TNC STRAIGHT  APVD: DATE BULKHEAD REAR MOUN		NC STRAIGHT JACK REAR MOUNT CLAMP TYPE -316DS & SIMILAR CABLES			
REFERENCE: ORIGINATED: D.N.		MATERIALS & FINISHES: SEE NOTES		size A	FSCM NO. 19505	DWG NO. 6001-7051-019 A
DATE: 05/09/18				SCALE	4:1	THIRD ANGLE SHEET 1 OF 1