



PAGE 1/2	ISSUE 04-12-19M	SERIES COUPLER	PART NUMBER R432172000
----------	------------------------	--------------------------	-------------------------------

Scale 1 : 1



All dimensions are in mm. Tolerances according ISO 2768 m-H

Weight **233,3200** g
Specification



ELECTRICAL CHARACTERISTICS

Frequency operating range :	0.15 – 0.30 GHz
Impedance :	50 Ω
VSWR : - Main Line	1.10 max.
- Coupled Line	1.10 max.
Nominal Coupling :	6 dB
Coupling Precision :	± 0.3 dB
Insertion Loss :	2 dB max.
Directivity :	30 dB mini
Frequency Sensitivity :	± 0.8 dB
Average Power at 25°C	500W
Peak Power at 25°C	5000W

MECHANICAL CHARACTERISTICS

Connector type :	N female per MIL-C 39012
Coaxial Termination :	SMA 50 Ω , 1W

ENVIRONMENTAL CHARACTERISTICS

Operating temperature :	-25°C / +70°C
Storage temperature :	-25°C / +70°C