


## **Technical Data Sheet**

50W 4-8GHZ 3DB HYBRID COUPLER

PAGE 1/2 ISSUE 29-09-17K SERIES COUPLER PART NUMBER R432631000

Scale 2:1



All dimensions are in mm. Tolerances according ISO 2768 m-H

Weight Specification **16,9000** g







50W 4-8GHZ 3DB HYBRID COUPLER

PAGE <b>2/2</b>	ISSUE <b>29-09-17K</b>	SERIES COUPLER	PART NUMBER <b>R432631000</b>
-----------------	------------------------	-------------------	-------------------------------

## **ELECTRICAL CHARACTERISTICS**

Frequency operating range:	4 – 8 GHz
Impedance:	50 Ω
VSWR	1.25 max.
Nominal Coupling :	3 dB
Insertion Loss:	0.3 dB max.
Isolation :	19 dB mini
Amplitude Balance :	$\pm 0.5 \text{ dB}$
Phase Balance:	90°±5°
Average Power at 25°C	50W
Peak Power at 25°C	3000W

## **MECHANICAL CHARACTERISTICS**

Connector type: SMA female per MIL-C 39012

## **ENVIRONMENTAL CHARACTERISTICS**

Operating temperature :	-25°C / +70°C
Storage temperature :	-25°C / +70°C