


Radiall **

50W 12.4-18GHZ 30DB DIRECTIONAL COUPLER







50W 12.4-18GHZ 30DB DIRECTIONAL COUPLER

PAGE 2 / 2	ISSUE 14-09-20A	SERIES COUPLER	PART NUMBER R433835000
--------------------------	------------------------	-------------------	-------------------------------

ELECTRICAL CHARACTERISTICS

Frequency operating range:	12.4 – 18 GHz
Impedance:	50 Ω
VSWR: - Main Line	1.35 max.
- Coupled Line	1.45 max.
Nominal Coupling :	30 dB
Coupling Precision:	± 1 dB
Directivity:	15 dB mini
Insertion loss:	0.5 dB max.
Frequency Sensitivity:	± 0.5 dB
Average Power at 25°C	50W
Peak Power at 25°C	3000W

MECHANICAL CHARACTERISTICS

Connector type:	SMA female per MIL-C 39012
Coaxial Termination:	SMA, 50 Ω, 1W

ENVIRONMENTAL CHARACTERISTICS

Operating temperature:	-25°C / +85°C
Storage temperature :	-40°C / +100°C