

## 4951.0 SI 6,3x32 0,125A-T



Fuse, Dimensions: 6.3x32 mm, Trigger characteristic: Slow-acting (T); Rated voltage: 500 / 440 / 250 V, Rated current: 0,125 A

### Business data

Article number	<u>4951.0</u>
Article name	SI 6,3x32 0,125A-T
GTIN (EAN)	4044211109134
Packaging unit	10
Quantity unit	PC
Weight per piece (not including packaging)	0.96 g
Weight per piece (including packaging)	1 g
Unit of weight	G
Customs number	85361010
Country of origin	EU
Product description	fuse

---

### Technical data

---

#### Dimensions

Length	31.8 mm
Diameter of contact cap	6.35 mm
Dimensions	6,3x32 mm

#### Ratings

Rated voltage	500 / 440 / 250 V
Rated current	0.125 A

#### Materials

Contact caps	Brass
Surface	Nickel
Tube	Ceramic

#### Further technical data

Trigger characteristic	Time-lag (T)
Rated breaking capacity	1,5 kA @ AC 500 (cosφ = 1 10 kA @ AC 440 V cosφ = 0,3)
Voltage drop	3400 mV
Power loss (@ 1.5 In)	1.4 W
Melting integral I <sup>2</sup> ts	0.06 A <sup>2</sup> s

#### Environmental Product Compliance

REACH Conform	yes
REACH Reference date	2023-06-14
REACH Candidate Substance Note	No
RoHS Conform	yes

# Data sheet

4951.0 SI 6,3x32 0,125A-T



---

Media

---

---

### Accessories

---