SPECIFICATIONS:

Insulation Resistance: 1,000M Ω min. at 500V DC Withstanding Voltage: 500Vrms for 1min

Voltage Rating: 5V DC

Current Rating: 0.5A

Contact Resistance: $100m\Omega$ max. at 20mV max.

Operating Temp.: - 25°C ~ +85°C

Mating Cycle: 10,000 times (general environment)

MATERIALS AND FINISH:

· Contacts: PB

· Metal Shell: Stainless Steel


· Insulator: LCP

FEATURES:

- · Dual-Phase Card-detection switch
- · Automotive Grade performance
- · RoHS and REACH Compliant


PART NUMBER:

FPS009-2960-0





OUTLINE DIMENSIONS (mm, With Card Detection Switch):





© 2020 Yamaichi Electronics USA Incorporated. All brand or product names may be trademarks of their respective companies.

Yamaichi Electronics USA Inc.

Visit Us @ WWW.YEU.COM

Email: Info@yeu.com

TEL: 408-715-9100