SPECIFICATIONS:

Insulation Resistance: $1,000M\Omega$ min. at 500V DC Withstanding Voltage: 500Vrms for 1min

Voltage Rating: 50 Vrms DC Current Rating: 0.5A

Contact Resistance: 100mΩ max. at 20mV max.

Operating Temp.: -20°C ~ +85°C

Mating Cycle:

➤ Indoor: 10,000 times

> None-indoor environment: 3,000 times

MATERIALS AND FINISH:

· Contacts: PB

· Metal Shell: Stainless Steel

· Insulator: LCP


FEATURES:

· Card-detection switch

- No circuit pattern prohibited layout area (2100*)
- Card-flyout prevention design (2120, 2130*)
- Push-Push R/A SMT mount
- · RoHS and REACH Compliant

PART NUMBER:

PJS008-21XX-0





OUTLINE DIMENSIONS (mm, WITH CARD DETECTION SWITCH):

