

SPECIFICATIONS:

Insulation Resistance: $500M\Omega$ min. at 500V DC Withstanding Voltage: 500V AC for 1min Voltage Rating: 10V MAX Current Rating: 0.5AContact Resistance: 80mohms initial Operating Temp.: $-25^{\circ}C \sim +85^{\circ}C$ Mating Cycle: 10,000 times

PART NUMBER:






MATERIALS AND FINISH:

- Contacts: Ni-Au/SnCu Alloy
- Insulator: LCP
- Metal Shell: Stainless Steel

FEATURES:

- Clam-Shell Locking mechanism
- RoHS and REACH Compliant

OUTLINE DIMENSIONS (mm):



© 2020 Yamaichi Electronics USA Incorporated. All brand or product names may be trademarks of their respective companies.

Yamaichi Electronics USA Inc. Visit Us @ WWW.YEU.COM Email: Info@yeu.com TEL: 408-715-9100

DISCLAIMER: PRODUCT DATA & DIMENSIONS ARE SUBJECT TO CHANGES WITHOUT NOTICE