



Fuse, Dimensions: 5x20 mm, Trigger characteristic: Fast-acting (F); Rated voltage: 250 V, Rated current: 0,125 A

Business data

| | |
|--|------------------|
| Article number | 2897.0 |
| Article name | SI 5x20 0,125A-F |
| GTIN (EAN) | 4044211056223 |
| Packaging unit | 10 |
| Quantity unit | PC |
| Weight per piece (not including packaging) | 0.96 g |
| Weight per piece (including packaging) | 1 g |
| Unit of weight | G |
| Customs number | 85361010 |
| Country of origin | EU |
| Product description | fuse |

Technical data

Dimensions

| | |
|-------------------------|---------|
| Length | 20 mm |
| Diameter of contact cap | 5.2 mm |
| Dimensions | 5x20 mm |

Ratings

| | |
|---------------|---------|
| Rated voltage | 250 V |
| Rated current | 0.125 A |

Materials

| | |
|--------------|--------|
| Contact caps | Brass |
| Surface | Nickel |
| Tube | Glass |

Further technical data

| | |
|--|-----------------------|
| Trigger characteristic | Fast-acting (F) |
| Rated breaking capacity | 35 A @ AC 250 V |
| Voltage drop | 350 mV |
| Power loss (@ 1.5 I _n) | 0.2 W |
| Melting integral I ² t _s | 0.01 A ² s |

Environmental Product Compliance

| | |
|--------------------------------|------------|
| REACH Conform | yes |
| REACH Reference date | 2023-06-14 |
| REACH Candidate Substance Note | No |
| RoHS Conform | yes |

Data sheet

2897.0 SI 5x20 0,125A-F



Approvals

Standards and regulations

Standards / specifications

IEC 60127-2/2 EN 60127-2/2 VDE 0820-2/2

Media

Accessories
