

4965.0 SI 6,3x32 3,150A-T



Fuse, Dimensions: 6.3x32 mm, Trigger characteristic: Slow-acting (T); Rated voltage: 500 / 440 / 250 V, Rated current: 3.15 A

Business data

| | |
|--|--------------------|
| Article number | <u>4965.0</u> |
| Article name | SI 6,3x32 3,150A-T |
| GTIN (EAN) | 4044211109271 |
| Packaging unit | 10 |
| Quantity unit | PC |
| Weight per piece (not including packaging) | 2.66 g |
| Weight per piece (including packaging) | 2.7 g |
| Unit of weight | G |
| Customs number | 85361010 |
| Country of origin | EU |
| Product description | fuse |

Technical data

Dimensions

| | |
|-------------------------|-----------|
| Length | 31.8 mm |
| Diameter of contact cap | 6.35 mm |
| Dimensions | 6,3x32 mm |

Ratings

| | |
|---------------|-------------------|
| Rated voltage | 500 / 440 / 250 V |
| Rated current | 3.15 A |

Materials

| | |
|--------------|---------|
| Contact caps | Brass |
| Surface | Nickel |
| Tube | Ceramic |

Further technical data

| | |
|------------------------------------|--|
| Trigger characteristic | Time-lag (T) |
| Rated breaking capacity | 1,5 kA @ AC 500 (cosφ = 1 10 kA @ AC 440 V cosφ = 0,3) |
| Voltage drop | 150 mV |
| Power loss (@ 1.5 In) | 1.4 W |
| Melting integral I ² ts | 37 A ² s |

Environmental Product Compliance

| | |
|--------------------------------|------------|
| REACH Conform | yes |
| REACH Reference date | 2023-06-14 |
| REACH Candidate Substance Note | No |
| RoHS Conform | yes |

Data sheet

4965.0 SI 6,3x32 3,150A-T



Media

Accessories
