



2X1 Dual Port RJ45 Connector with No Magnetics AR21NM-4474I



- 2x1 Stacked RJ45 without Magnetics
- Industrial Operating Temp: -40°C to +85°C

Electrical Specifications @ 25°C

Part Number	Voltage Rating (VAC RMS)	Current Rating (Amp)	Contact Resistance (Max)	Insulation Resistance (Min @ 500 VDC)	Dielectric Strength Contact to Contact @ .5mA 50Hz or 60Hz / 60Sec
AR21NM-4474I	150	1.5	20mΩ	1000MΩ	1000VDC or VAC Peak

All specifications subject to change without notice.

MECHANICAL

Dimension Unit: mm



