



## PRODUCT SPECIFICATIONS

SEMICONDUCTOR TECHNOLOGY, INC.  
 3131 S. E. JAY STREET, STUART, FL 34997  
 PH: (561)283-4500 FAX: (561)286-8914  
 Website: <http://www.semi-tech-inc.com>

TYPE: MJH16012

CASE OUTLINE: TO-218

### NPN SILICON HIGH VOLTAGE POWER TRANSISTOR

#### ABSOLUTE MAXIMUM RATING:

Collector to Base Voltage	$BV_{CBO}$		Vdc
Collector to Emitter Voltage	$BV_{CEV}$	850	Vdc
Emitter to Base	$BV_{EBO}$	6.0	Vdc
Collector to Emitter	$BV_{CEO(sus)}$	450	Vdc
Continuous Collector Current	$I_C$	15	Adc
Peak Collector Current	$I_{CM}$	20	Adc
Power Dissipation $T_A = 25\text{ }^\circ\text{C}$	$P_D$	135	Watts
Power Dissipation $T_C = 25\text{ }^\circ\text{C}$	$P_D$		Watts
Storage Temperature	$T_{stg}$	-55 to +150	$^\circ\text{C}$
Operating Temperature	$T_J$	-55 to +150	$^\circ\text{C}$
Lead Temperature From Case	$T_L$	275	$^\circ\text{C}$

#### ELECTRICAL CHARACTERISTICS $T_A @ 25\text{ }^\circ\text{C}$

PARAMETERS	SYMBOL	TEST CONDITIONS	MIN	TYP	MAX	UNIT
Collector to Base Voltage	$BV_{CBO}$					Vdc
Emitter to Base Voltage	$BV_{EBO}$					Vdc
Collector to Emitter Voltage	$BV_{CEO(sus)}$	$I_C = 100\text{mA}$ $I_B = 0$	450			Vdc
Collector to Emitter Voltage	$BV_{CEO}$					Vdc
Collector to Emitter Voltage	$BV_{CEV}$					Vdc
Collector Cutoff Current	$I_{CER}$	$V_{CE} = 850\text{V}$ $R_{BE} = 50\Omega$ $T_C = 100\text{ }^\circ\text{C}$			2.5	mA
Collector Cutoff Current	$I_{CBO}$					mA
Collector Cutoff Current	$I_{CEV}$	$V_{CEV} = 850\text{V}$ $V_{BE(OFF)} = 1.5\text{V}$			0.25	mA
Collector Cutoff Current	$I_{CEV}$	$V_{CEV} = 850\text{V}$ $V_{BE(OFF)} = 1.5\text{V}$ $T_C = 100\text{ }^\circ\text{C}$			1.5	mA
Collector Cutoff Current	$I_{CEX}$					mA
Emitter Cutoff Current	$I_{EBO}$	$V_{EB} = 6.0\text{V}$			10	mA
D.C. Current Gain Pulsed*	$h_{FE}$	$I_C = 15\text{A}$ $V_{CE} = 5.0\text{V}$	5.0			-
D.C. Current Gain Pulsed*	$h_{FE}$					-
D.C. Current Gain Pulsed*	$h_{FE}$					-
D.C. Current Gain Pulsed*	$h_{FE}$					-
D.C. Current Gain Pulsed*	$h_{FE}$					-
Saturation Voltage*	$V_{CE(sat)}$	$I_C = 5.0\text{A}$ $I_B = 0.7\text{A}$			2.5	Vdc
Saturation Voltage*	$V_{CE(sat)}$	$I_C = 10\text{A}$ $I_B = 1.3\text{A}$			3.0	Vdc
Saturation Voltage*	$V_{CE(sat)}$	$I_C = 10\text{A}$ $I_B = 1.3\text{A}$ $T_C = 100\text{ }^\circ\text{C}$			3.0	Vdc
Base Emitter Voltage*	$V_{BE(sat)}$					Vdc
Base Emitter Voltage*	$V_{BE(sat)}$	$I_C = 10\text{A}$ $I_B = 1.3\text{A}$			1.5	Vdc
Base Emitter Voltage*	$V_{BE(sat)}$	$I_C = 10\text{A}$ $I_B = 1.3\text{A}$ $T_C = 100\text{ }^\circ\text{C}$			1.5	Vdc
Base Emitter Voltage*	$V_{BE(on)}$					Vdc

Notes: \*Pulse Width  $\leq 300\mu\text{sec}$  2% Duty Cycle



TYPE: MJH16012

**SMALL SIGNAL CHARACTERISTICS**

	SYMBOL	MIN	TYP	MAX	UNITS
Current Gain at F =	$h_{fe}$				-
Input Capacitance	$C_{ib}$				pf
Output Capacitance $V_{CB} = 10V$ $I_E = 0$ $f_{test} = 1.0KHz$	$C_{ob}$			400	pf
Transition Frequency	$f_T$				MHz
Input Impedance					Ohms
Voltage Feedback Ratio					X10-4
Output Admittance					$\mu mhos$
Noise Figure	NF				dB

**SWITCHING CHARACTERISTICS**

<b>Resistive Load</b>			SYMBOL	MIN	TYP	MAX	UNITS
Storage Time	$I_C = 10A$ $V_{CC} = 250V$ $I_{B1} = 1.3A$ $P_W = 30\mu s$ $DC \leq 2\%$	$V_{BE(OFF)} = 5.0V$	$t_s$		650		ns
Fall Time			$t_f$		80		ns
Delay Time			$t_d$		20		ns
Rise Time		$I_{B2} = 2.6A$ $R_{B2} = 1.6\Omega$	$t_r$		200		ns
Storage Time			$t_s$		1200		ns
Fall Time			$t_f$		200		ns
<b>Inductive Load</b>			SYMBOL	MIN	TYP	MAX	UNITS
Storage Time	$I_C = 10A$ $I_{B1} = 1.3A$ $V_{BE(OFF)} = 5.0V$ $V_{CE(pk)} = 400V$	$T_C = 100^\circ C$	$t_{sv}$		800	1800	ns
Crossover Time			$t_c$		90	250	ns
Fall Time			$t_{fi}$		50	200	ns
Storage Time		$T_C = 150^\circ C$	$t_{sv}$		1050		ns
Crossover Time			$t_c$		120		ns
Fall Time			$t_{fi}$		70		ns

**FUNCTIONAL TEST**

	SYMBOL	MIN	TYP	MAX	UNITS
Common-Emitter Amplifier Power Gain	GPE				dB
Power Output	Pout				Watt
Collector Efficiency	$\eta$				%
Power Output	Pout				Watt
Second Breakdown Collector Current	$I_{S/B}$				A
Thermal-Resistance, Junction to Case	$R_{\theta JC}$			0.93	$^\circ C/W$