Type CNX-02 PC Board Type Fuse Clips Maxi Auto Blade Fuses

www.optifuse.com

(619) 593-5050

Specifications:

Rating: 80A, 500V AC / 250V DC Body Material: Phosphor Bronze


Molded Parts: Glass filled Nylon UL94V-0

Finish: Bright Tin plated

(For Matte Tin plated – Part number CNX-02-CE)

For use with Type **APX** Fuses (Maxi-Automotive Blade Type)

Mechanical Dimensions: Inches [mm]



Warning:

-Operation beyond the specified maximum ratings or improper use may result in damage and possible electrical arcing and/or flame.



-Avoid contact of device with chemical solvent. Prolonged contact may damage the device performance.