Type LPA-08 In-Line Fuse Holder 1/4" x 11/4" (6.3 x 32mm) Fuses



www.optifuse.com

(619) 593-5050

Ratings:

Fuse Type: 1/4" x 11/4" (6.3 x32mm) Electrical Rating: 250VAC, 32VDC

Body: Polycarbonate **Contacts:** Brass

Standard Wire Sizes: #14 ~ #18 AWG

Standard Wire Colors: Red

Standard Body colors: Red and Black **Standard Wire Length:** 6 inches

Part number format LPA-08X-##Z


where **X** = Body color ## = Wire gauge **Z** = Wire color


Wire Gauge	Max. Amperage
14 AWG	20 A
16 AWG	15 A
18 AWG	10 A

Available in various wire gauges and lengths, and body and wire colors.

Contact factory for those not listed above.

Mechanical Dimensions: Inches [mm]





Warning:

-Operation beyond the specified maximum ratings or improper use may result in damage and possible electrical arcing and/or flame.



- -Avoid contact of device with chemical solvent. Prolonged contact may damage the device performance.
- -Not designed for prolonged liquid exposure or submersible applications.

Note: All specifications subject to change without notice. Rev C 11/2021 - Page: 1/1

Code J01-02D