## Type PMA-KB-08-Q1S Panel Mount Fuse Holder 1/4" x 11/4" (6.3 x 32mm) Fuses Knob / Bayonet



www.optifuse.com

(619) 593-5050

Electrical Rating: 10A, 250V AC Fuse Style: '4" x 1'4" (6.3 x 32mm)

**Material:** 

Frame and Cap: Thermoplastic Material (UL flame: 94V-0)

**Terminals:** Nickel or Tin-plated Copper Alloy


**Cap:** Knob type, Bayonet type **Mounting:** Snap Fit Mounting

**Terminal:** Solder/Quick-Connect 4.8mm / 0.187"


**Agency Standards and Listings:** 



**Product Dimensions: Inches [mm]** 



## **Panel Cutout**



| Panel<br>Thickness | X            | Y            |
|--------------------|--------------|--------------|
| .039 [1.0]         | .547 [13.9]  |              |
| .059 [1.5]         | .563 [14.3]  | 591 +.004/-0 |
| .079 [2.0]         | .570 [14.5]  |              |
| .098 [2.5]         | .577 [14.65] | [15 +0.1/-0] |
| .118 [3.0]         | .583 [14.8]  |              |
| .138 [3.5]         | .591[15.0]   |              |

## Warning:

-Operation beyond the specified maximum ratings or improper use may result in damage and possible electrical arcing and/or flame.



-Fuse Holders are not intended for circuit disconnect. All power should be disconnected before removing fuse.

-Avoid contact of Fuse Holder with chemical solvent. Prolonged contact may damage the device performance.

Note: All specifications subject to change without notice.

Rev A 08/2011 - Page: 1/1 Code G01-01H