Type LPR-03 In-Line Fuse Holder Automotive Blade Fuses - APRs Splashproof Type



www.optifuse.com

(619) 593-5050

Ratings:

Fuse Type: Automotive Blade – APRs, ANRs

Electrical Rating: 30A 58VAC

The Ambient Temperature: -40°C to +85°C

Body: PVC

Cap: Splashproof type

IP Rating: IP65

Wire Sizes: # 10, # 12, # 14, #16, #18 AWG, UL 1015

Standard Wire Colors: Red, Black **Standard Body Colors:** Red, Black

Wire Length: 12 inches – End to End Loop

Available in various wire gauges and lengths, and body and wire

colors. Contact factory for those not listed above.

Mechanical Dimensions: Inches [mm]


Part number format LPR-03X-##Z

Where X = Body color - Red, Black

= Wire gauge

 $\mathbf{Z} = \text{Wire color}(\mathbf{R} \text{ or } \mathbf{B})$

Wire	Max.
Gauge	Amperage
10 AWG	40 A
12 AWG	30 A
14 AWG	20 A
16 AWG	15 A
18 AWG	10 A



Warning:

-Operation beyond the specified maximum ratings or improper use may result in damage and possible electrical arcing and/or flame.



-Avoid contact of device with chemical solvent. Prolonged contact will damage the device performance.

-Not designed for prolonged liquid exposure or submersible applications.

Note: All specifications subject to change without notice.

Rev E 12/2022 - Page: 1/1 Code G02-01H