## Type PMC-DS-05-SOR (formerly PDC-02) **Panel Mount Fuse Holder** 5 x 20 mm Fuses **Driver / Screw**



www.optifuse.com

(619) 593-5050

Electrical Rating: 10A, 250V AC

**Fuse Style:** 5 x 20mm

**Material:** 


Frame and Cap: Phenolic (UL flame: 94V-2)

**Terminals:** Tin-plated brass Cap: Slotted Driver type, Screw type

Mounting: by nut

**Terminal:** Solder 4.00mm / 0.156" **Panel Thickness:** 4.5mm MAX **Agency Standards and Listings:** 





## Warning:

-Operation beyond the specified maximum ratings or improper use may result in damage and possible electrical arcing and/or flame.



-Fuse Holders are not intended for circuit disconnect. All power should be disconnected before removing fuse. -Avoid contact of Fuse Holder with chemical solvent. Prolonged contact may damage the device performance.

Note: All specifications subject to change without notice.

Rev A 01/2008 - Page: 1/1 Code S02-02D