Type BLR-I-310 Fuse Block - Indicating 10 Pole - Regular Auto Blade

www.optifuse.com

(619) 593-5050

Specifications:

Max Current Rating: 30A per Circuit - 100A Max Input Fuse Type: Regular Auto Blade – APR, ANR Series

Base: PBT (UL flame: 94V-0), Black **Cover:** PC (UL flame: 94V-2), Transparent


Push Button: POM (White)

Terminals: Copper, Tin plated 0.250" Quick Connect Terminals

Indicating LED – Red

Ambient/Operating Temperature: -20 °C to +85 °C

Mechanical Dimensions: Inches [mm]



Warning:

-Operation beyond the specified maximum ratings or improper use may result in damage and possible electrical arcing and/or flame.



-Avoid contact of device with chemical solvent. Prolonged contact may damage the device performance.

Note: All specifications subject to change without notice.

Rev C 05/2017 - Page: 1/1 Code S02-01H