Type CNU-03 PC Board Type Fuse Clip Auto Blade Fuses - Universal



www.optifuse.com

(619) 593-5050

Specifications:


Rating: 30A, 500V AC


Body Material: PBT, UL Rated 94 V-0 Contacts: 0.4mm thick Brass, Tin-plated Temperature Rating: -50°C~+145°C


For use with Automotive Blade Type Fuses:

APM / ANM (Mini), APS / ANS (Mini Low Profile), APR / ANR (Regular)


Mechanical Dimensions: Inches [mm]







Mounting Detail



Warning:

-Operation beyond the specified maximum ratings or improper use may result in damage and possible electrical arcing and/or flame.



-Avoid contact of device with chemical solvent. Prolonged contact will damage the device performance.