Type LPA-07 In-Line Fuse Holder ¼" x 1¼" (6.3 x 32mm) Fuses



www.optifuse.com (619) 5


where ## = Wire gauge


Part number format LPA-07B-##R (619) 593-5050

Ratings:

Fuse Type: ¹/4" x 1¹/4" (6.3 x32mm) Electrical Rating: 30A, 250VAC, 100VDC Body: Bakelite Contacts: Brass (UL94V-0) Standard Wire Sizes: #10 ~ #20 AWG Standard Wire Colors: Red Standard Body colors: Black Standard Wire Length: 4 inches Available in various wire gauges, lengths and colors. Contact factory for those not listed above.

Mechanical Dimensions: Inches [mm]





Warning:

-Operation beyond the specified maximum ratings or improper use may result in damage and possible electrical arcing and/or flame.

-Avoid contact of device with chemical solvent. Prolonged contact may damage the device performance.