Type LPX-02 In-Line Fuse Holder Maxi Automotive Blade Fuses Splashproof Cap, Ignition Protected



www.optifuse.com

(619) 593-5050

Ratings:

Fuse Type: Maxi Automotive Blade - APXs, ANXs

Electrical Rating: 58VDC

Ambient/Operating Temperature: -40 °C to +85 °C

Body: PVC

Contacts: Brass with Tin Plated

Cap: Splashproof Cap **IP Rating:** IP65 **Ignition Protected**

Standard Wire Sizes: #6 ~ #8 AWG Standard Wire Colors: See table Standard Body colors: Black **Standard Wire Length:** 5 inches

Available in various wire gauges and lengths, and body and wire colors. Contact factory for those not listed above.


Mechanical Dimensions: Inches [mm]

Part number format LPX-02B-##Z

where ## = Wire gauge

 \mathbf{Z} = Wire color (\mathbf{R} or \mathbf{B})

Standard Colors for Wire Gauges		
AWG	Standard Wire Color	Max Amperage
#6	Red	80A
#8	Black	60A



Warning:

-Operation beyond the specified maximum ratings or improper use may result in damage and possible electrical arcing and/or flame.



-Avoid contact of device with chemical solvent. Prolonged contact may damage the device performance.

-Not designed for prolonged liquid exposure or submersible applications.

Note: All specifications subject to change without notice.

Rev G 02/2021 - Page: 1/1

Code J01