Type BLR-I-610 Fuse Block - Indicating 10 Pole - Regular Auto Blade



www.optifuse.com

(619) 593-5050

Specifications:

Fuse Type: Regular Auto Blade – APR, ANR Series

Max Current Rating: 30A per Circuit - 100A Max Input

Max Voltage: 32VDC

IP Rating: 40 Material: Base: PBT

Terminals: Copper, tin plated


0.250" [6.3mm] Quick Connect Terminals


Cover: PC (Transparent) **Indicating LED** – Red

Temperature Rating: -20° C $\sim +85^{\circ}$ C

Mounting: Two (2) 5 mm mounting holes for #10 screws

Mechanical Dimensions: Inches [mm]





Warning:

-Operation beyond the specified maximum ratings or improper use may result in damage and possible electrical arcing and/or flame.



-Avoid contact of device with chemical solvent. Prolonged contact may damage the device performance.

Note: All specifications subject to change without notice.

Rev A 05/2018 - Page: 1/1 Code S02-01H