

# MIDI 498 IL SERIES

## 58V IN-LINE FUSE HOLDER



04980921GXM5

### Description

The MIDI® 498-IL Series 58V In-Line Fuse Holder can be installed directly in line with the cables to provide high-amperage main or branch circuit protection in harsh or hazardous environments. Because there's no need to mount the fuse holder, it saves both time and space.

With a curved cover that helps prevent tube splitting, the MIDI® 498-IL Series fuse holder is specifically designed for use with heat shrink tubing (sold separately) in applications that need added splash protection.

This high-amp automotive fuse holder features a UL 94 V-0 rated glass-filled nylon base and cover and accepts M5 MIDI® bolt-down fuses rated up to 200 amps.

### Web Resources

Download 2D print, installation guide and technical resources at: [littelfuse.com/498-IL](https://www.littelfuse.com/498-IL)

### Ordering Information

PART NUMBER	DESCRIPTION	FUSE TYPE	MOUNTING METHOD	MAX CURRENT RATING	MAX VOLTAGE RATING
04980921GXM5	58V In-Line Fuse Holder with Cover and Hardware	MIDI FUSES	IN-LINE FUSE HOLDER	200 AMPS	58V
498921-1	Fuse Holder Cover	-	-	-	-
498921-2	58V In-Line Fuse Holder Base with Zinc-Plated Steel Hardware	-	In-Line	-	-
498921-3	58V In-Line Fuse Holder Base - No Hardware	-	In-Line	-	-

### Specifications

<b>Current Rating Continuous:</b>	150A
<b>Current Rating Max:</b>	200A
<b>Fuse Type:</b>	BF1 / MIDI M5 Fuses
<b>Flammability Rating:</b>	UL 94 V-0
<b>Mounting Method:</b>	Nuts and Bolts
<b>Max Voltage Rating:</b>	58V

### Applications

- High-Amp Circuit Protection
- Automotive Circuit Protection

### Features and Benefits

- Compatible with M5 MIDI® bolt-down fuses rated up to 200 amps (sold separately)
- Installs directly in line with cables, which eliminates the need to mount the fuse holder
- Curved cover helps prevent tube splitting when using heat shrink tubing (sold separately) to achieve added splash resistance
- Zinc-plated steel M5 bolts and M5 nylock nuts offer long-term corrosion resistance
- Available as a complete fuse holder assembly and as component parts to meet various installation requirements