Type LPS-08-3 "Add-On" Automotive Fuse Holder Low Profile Mini Auto Blade Fuse Total 3 Circuits




www.optifuse.com (619) 593-5050

For use with Type APS, ANS Fuses (Low Profile Mini Automotive Blade) Rating: 58V Max Installation Current Rating:

- Existing Circuit: 30A
- Add-on Circuit: 20A

Body Material: Nylon with Glass Fiber (UL 94V-0), Black Terminals: Brass, Tin plated Wire: # 16 AWG UL 1015 Red Wire Connector: Butt-Splice Connector

Mechanical Dimensions: Inches [mm]



 Warning:
 -Operation beyond the specified maximum ratings or improper use may result in damage and possible electrical arcing and/or flame.

 -Device is intended for occasional overcurrent protection. Application for repeated overcurrent condition and/or prolonged trip are not anticipated.

 -Avoid contact of device with chemical solvent. Prolonged contact will damage the device performance.

Note: All specifications and dimensions subject to change without notice.

Rev A 10/2017 - Page: 1/1 Code G02-01H